

Cold Light Source KL 1600 LED Packages Schott

[Product in eShop](#)

Home / [Labortops_Q1_2025](#) / Cold Light Source KL 1600 LED Packages Schott

Product Data

The KL 1600 LED is an innovative fiber optic light source which uses cold light to illuminate all types of objects in industrial and life science applications.

- Powerful illumination system with a brightness of 680 lm
- Ergonomically placed dimming control
- Ripple free illumination for digital imaging applications
- Colour temperature of 5,600 K does not change when the light source is dimmed
- Maintenance free due to long lifetime LEDs of 50,000 hours

Scope of supply:

LED Cold light source KL 1600 LED incl. 2-armed gooseneck light guide, 2 focus lenses, according power cord

Specifications

Colour temperature: 5600 K

Light flux: 680 lm

Dimensions KL 1600 LED (W x D x H): 114 x 231 x 137 mm

Dimensions light guide (Ø x L): 4.5 x 600 mm

Weight: 3.9 kg

Power supply: 100 ... 240 V, 50/60 Hz

Item No.	type no.	Price
10.4666.29	KL 1600 LED paket - connector type CH	CHF 1'635.00
17.9922.01	KL 1600 LED paket - plug type EU	CHF 1'648.70

* The prices are non-binding and are to be understood as selling prices in Swiss francs without value added tax (VAT), as well as all other fees, charges and taxes. The prices displayed in the eShop may differ from the PDF file due to regular updates.

** Please note that when ordering chemicals and detergents, transport and packaging costs for hazardous goods as well as legally prescribed fees are charged. These will be shown in detail on the order confirmation, which you will receive in addition to the confirmation of receipt.

*** Further information such as technical information and safety data sheets can be found online in our eShop.

**** The PDF file was created on www.huberlab.ch on 22.04.2026 at 09:38 oclock.

www.huberlab.ch